

SILPAK SILPUTTY 40

Kneadable Platinum Silicone Dough

Silputty 40 is a platinum-based, two-component, 1:1 mix ratio by weight, food safe, quick curing silicone RTV that captures forensic detail. Simply knead A and B components together and press on to surface.

Features

- Kneadable dough
- Simple Mix Ratio
- High detail capture

Applications

Use for making molds and impressions including anything where a quick temporary mold or rubber part may be required. Molds can be used to cast all types of resins, wax and plaster materials.

- Custom rapid prototypes
- Architectural restoration
- Food molds
- Texture pads
- Tool fixtures
- Quick impressions
- Calibration impressions

Physical and Handling Properties

Property	Value
Color	Green
Mix Ratio, by weight	1 Base : 1 Activator
Mix ratio by volume	1 Base : 1 Activator
Initial Viscosity, Base, cP	Kneadable Dough
Initial Viscosity, Activator, cP	Kneadable Dough
Initial Mixed Viscosity, at 77°F, cP	Kneadable Dough
Hardness, Shore A	40
Gel Time, min	5
Cure Time, min	10
Specific Gravity	1.5
Elongation, %	100
Tear Resistance, pli	30

Values listed above are typical and not intended for use in specifications.



Proper Use and Safety

Read all instructions and safety data sheets prior to use. Consult safety data sheets for all recommended safety precautions.

Mixing & Curing

Mix 1 part by weight of base to 1 part by weight of activator, a visual estimation of proportions is usually sufficient. Knead components together until color is uniform. Be careful not to mix more than can be applied in 3 minutes. Press material into desired surface, taking care to avoid air entrapment and allow to cure. Hot or cooler temperatures will affect cure and gel times. Heat from hair dryer can be used to accelerate cure. Requirements for cure are dependent on the application and should be determined by the user.

See Addition Cure Tech Sheet for additional information.

Inhibition

Certain materials will cause inhibition or neutralizing of the curing agent, including sulfur and organo-metallic salt containing compounds (found in organic rubbers), many condensation-cure RTV, chloride solvents and amines. Avoid using latex gloves, water-based clays and tin/condensation cured RTVs. Inhibition may easily be determined by brushing a small quantity of this material over the surface and allowing it to cure. If material remains tacky and gummy after the curing time, then the part's surface is acting as an inhibitor.

See Addition Cure Technical Data Sheet for inhibiting materials.

Storage and Shelf Life

Base and Activator must be stored in their original, tightly closed containers to protect from moisture and foreign materials. Storage area should be maintained at temperatures between 64-86°F. Shelf life of materials when kept in unopened, sealed containers, at the recommended storage conditions, is six months. Containers should not be opened until ready or use. Once opened, storage life can be extended with the use of purging gas, such as nitrogen.

DISCLAIMER: the information and data contained herein are based on information we believe is reliable. Each user of the material should thoroughly test application, and independently conclude satisfactory performance before commercializing. Suggestions of uses should not be taken as inducements to infringe on any patent. Silpak or Polytek Development Corp make no warranty expressed or implied, including warranties of merchantability or fitness for a particular use. Under no circumstances will Silpak or Polytek Development Corp. be liable for incidental, consequential or other damages, alleged negligence, breach of warranty, strict liability, tort, or any other legal theory arising out of the use or handling of this product.